

# tesa® 6256

# **Product Information**



## Dispenser para cierre de bolsas

# Descripción del producto

Cualquier bolsa de plástico o de papel con un diámetro de cuello de hasta 6 mm se puede precintar eficazmente con el cierra bolsas tesa <sup>®</sup> 6256. Para este dispensador se recomienda usar las cintas tesa <sup>®</sup> film 4104 o 4205; y la cinta de papel tesa <sup>®</sup> 4328.

#### Características

Any plastic or paper bag with a twisted neck diameter of up 6 mm can be sealed effectively using the tesa® 6256 bag sealer. Recommended tesa® products: filmic tapes, tesa® 4104 or 4205; paper tape, tesa® 4328

# **Aplicación**

The tape is placed with the adhesive side up. The twisted neck of the bag is pulled down through the slot of the unit and thus closed by a tab seal securely taped to the bag neck.

### Propiedades / Valores de rendimiento

	•				
•	Core diameter	3	•	Modo de operación	manual
•	Diámetro máximo del rollo	130 mm	•	Roll width max	12 mm
•	Gramaje	610 g	•	Tipo de aplicación	embalaje

## Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

