



**Product Information** 



# 200µm double sided transparent PET film tape with 90% PCR PET content in backing

## Deskripsi Produk

tesa® 51966 is a transparent double-sided industrial mounting tape with a 90% post-consumer recycled (PCR) PET backing and a highly tackified acrylic adhesive. The double-sided tape is especially designed for converter and tape specialist business and is able to withstand numerous environmental factors such as humidity, UV light and temperatures of up to 130°C for limited periods of time. The tackified acrylic adhesive provides excellent adhesion on various surfaces, very high tack, and good shear strength. tesa® 51966 contains an average of 8% post-consumer recycled content, consisting of 90% recycled PET backing. Liner and tape core are considered packaging materials and are excluded from recycled content calculations. This is a third-party environmental claim validated against the UL Environmental Claim Validation Procedure 2809 for recycled content. The UL Environmental Claim Validation Program falls under UL's ISO/IEC 17025 accreditation. Find more information on the UL SPOT® database https://spot.ul.com/main-app/products/ detail/62a340de7501b678a13670cb?page\_type=Products%20Catalog

#### **Product Features**

- Excellent combination of high initial tack and immediate adhesion
- Full suitability for long-term applications
- Outstanding converting properties

#### Penerapan

- Various industrial long-term mounting applications
- Especially designed for converter and tape specialist business

## Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

## Konstruksi Produk

• Type of adhesive

PET film

- Berbasis Bio (konten karbon-bio) acrylic
- Total thicknessColor

200 µm transparent

<sup>2</sup>age 1 of 2 – as of 27/02/24 – id-ID





**Product Information** 

#### Properti / Nilai Kinerja

<ul> <li>Elongation at break</li> <li>Tensile strength</li> <li>Ageing resistance (UV)</li> <li>Chemical Resistance</li> <li>Durasi ketahanan suhu jangka panjang</li> <li>Durasi ketahanan suhu jangka pendek</li> </ul>	55 % 20 N/cm good good 80 °C 130 °C	<ul> <li>Humidity resistance</li> <li>Softener resistance</li> <li>Static shear resistance at 23°C</li> <li>Static shear resistance at 40°C</li> <li>Tack</li> <li>Temperature resistance min.</li> </ul>	very good good good very good -40 °C
Adhesi pada Nilai			
<ul> <li>ABS (initial)</li> <li>ABS (after 14 days)</li> <li>Aluminium (initial)</li> <li>Aluminium (after 14 days)</li> <li>PC (initial)</li> <li>PC (after 14 days)</li> <li>PE (initial)</li> <li>PE (after 14 days)</li> <li>PET (initial)</li> </ul>	10.5 N/cm 11.5 N/cm 9 N/cm 10 N/cm 13 N/cm 13.5 N/cm 7 N/cm 7.5 N/cm 9 N/cm	<ul> <li>PET (after 14 days)</li> <li>PP (initial)</li> <li>PP (after 14 days)</li> <li>PS (initial)</li> <li>PS (after 14 days)</li> <li>PVC (initial)</li> <li>PVC (after 14 days)</li> <li>Steel (initial)</li> <li>Steel (after 14 days)</li> </ul>	9.5 N/cm 7.5 N/cm 8 N/cm 11 N/cm 12 N/cm 9 N/cm 13 N/cm 10.5 N/cm 11 N/cm

## **Additional Information**

Liner variants:

- PV06: red MOPP film (80μm; 72g/m<sup>2</sup>)
- PV20: branded brown paper (69μm; 80g/m<sup>2</sup>)

According to VDA278 analysis, tesa 51966 does not contain any single substances restricted by the drafted GB regulations (China) as well as the indoor concentration guideline by Health, Labour and Welfare Ministry (Japan).

## Disclaimer

tesa<sup>®</sup> products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa<sup>®</sup> product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



<sup>2</sup>age 2 of 2 – as of 27/02/24 – id-ID