



**Product Information** 



# $250 \ \mu m$ plate mounting tape

### **Product Description**

tesa® 52310 (transparent), tesa® 52315 (yellow), tesa® 52320 (white) and tesa® 52325 (light pink) are a range of tesaprint® plate mounting tapes, each of a different thickness category.

Since the specially designed adhesive does not reach its final adhesion level immediately, plates can be easily repositioned during plate mounting. Later during printing, the final adhesion has been reached, ensuring secure plate bond and no edge lift.

The tesaprint<sup>®</sup> products can be used for various applications, e.g. plate mounting on compressible sleeves, letterpress plate mounting, or dry offset blanket mounting.

### **Product Features**

- They all feature PVC backings and rubber adhesives and are equipped with a structured PP liner, which prevents the formation of air pockets during plate mounting.
- After printing, the tesaprint<sup>®</sup> products are easily removable and do not leave residues.

## **Application Fields**

Plate mounting for various applications

### Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

### **Product Construction**

٠	Backing material	PVC film	٠	Type of liner	PP
٠	Type of adhesive	natural rubber			

#### **Properties/Performance Values**

Thickness category 250





**Product Information** 

## Disclaimer

tesa<sup>®</sup> products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa<sup>®</sup> product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



Page 2 of 2 – as of 01/04/25 – en-SA