



tesa® Spare Glass For Toilet Brush

Product Information

BNR 40337

Product Description

With this spare glass you are able to replace your toilet brush glass without buying a whole new toilet brush set. With this spare glass you are able to replace your toilet brush glass without buying a whole new toilet brush set.

Product Features

- Spare glass for toilet brush for use in the tesa® toilet brush sets
- Round style, satined glass
- Dimensions of the glass: 160mm x 94mm x 94mm
- For conventional toilet brushes up to max. Ø 75mm
- Suitable for holders with a diameter of 85mm
- For the tesa® series Elegaat, Esteetic, Excellent, Nooblesse, Klaam and Smooz® Spare glass for toilet brush for use in the tesa® toilet brush sets
- Round style, satined glass
- Dimensions of the glass: 160mm x 94mm x 94mm
- For conventional toilet brushes up to max. Ø 75mm
- Suitable for holders with a diameter of 85mm
- For the tesa® series Elegaat, Esteetic, Excellent, Nooblesse, Klaam and Smooz

Application Fields

||

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

- Type of adhesive none

Properties/Performance Values

• Applicationfield	Bathroom	• Material	Frosted glass
• Chemical resistance	no	• Reusable	yes
• Curing time	12 hour(s)	• Solvent free	yes
• Design series	tesa® KLAAM	• UV-resistant	yes
• Hazard material	no		



tesa® Spare Glass For Toilet Brush

Product Information

Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

For latest information on this product please visit <http://l.tesa.com/?cp=NaN>