



tesa® Baboo Storage Box XL, Self-Adhesive, Bamboo & High-Quality Plastic



Product Information

BNR 40524

Product Description

The extra large tesa® Baboo box uses the drill-free, easy-to-mount tesa® Powerstrips Waterproof technology. A mixture of bamboo and high-quality matt white plastic underlines the urban design. Keep bathroom essentials well organised with this storage container that comes with a divider. tesa® Powerstrips Waterproof is a powerful and water-resistant adhesive solution with a hold of up to 3 kg. The strips are easy to remove and residue-free. tesa® Baboo boxes are available in different sizes to mix and match for a complete space-saving bathroom storage solution. The box may be remounted using tesa® Powerstrips Waterproof XL refill strips.

Product Features

- Storage box with tesa® Powerstrips Waterproof technology (all-in-one adhesive mounting solution), 3 kg max. holding power
- Box with lid and extra large size offers enough space to store larger toiletries, flexible divider included for box content organisation
- Modern design, urban material mix – natural bamboo lid paired with matt white high-quality plastic box
- Space-saving bathroom storage solution for keeping bathroom essentials well organised and easy to reach
- Reliable, durable wall mounting, easy, clean and fast to install, no drilling needed, removable without a trace, no surface damage
- Adheres to glazed tiles, marble, metal, glass, wood, and plastics (ABS, PS, acrylic glass)
- Not suitable for stone, cement, wallpaper, plaster, enamel varnish and plastics such as PP, PE and PTFE
- Reusable after removal with new tesa® Powerstrips Waterproof XL strips – available separately as a refill pack
- tesa® Baboo boxes are available in different sizes
- Product dimensions: 242mm x 160mm x 102mm

Application Fields

Mounting

1. Clean the surface with alcohol or silicone-free glass cleaner
2. Wipe the waterproof primer over the surface using the primer tissue and wait for 10 seconds to allow the primer to evaporate
3. Attach the Powerstrips® to the base plates of the box – press firmly for a minimum of 5 seconds
4. Remove the cover sheets from the Powerstrips®
5. Position the box on the surface and press firmly towards the wall
6. Slide the box upwards and take it off the base plates – press the base plates firmly for a minimum of 5 seconds
7. Position the box on the base plates and slide it down until it snaps into place

Disassembly

1. Slide the box upwards and take it off the base plates
2. First stretch the tab of the Powerstrip® to around 3–5 cm, hold the base plate tight – don't press it on, and keep stretching the Powerstrip® parallel to the surface (do not pull strip away from the surface, as Powerstrip® may rip)

For latest information on this product please visit <http://l.tesa.com/?cp=NaN>



tesa® Baboo Storage Box XL, Self-Adhesive, Bamboo & High-Quality Plastic

Product Information

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

• Type of adhesive	synthetic rubber	• Special features	with partition
• Holding power up to	3 Kg	• Splashproof	yes

Properties/Performance Values

• Chemical resistance	no	• Residue free removal	yes
• Curing time	12 hour(s)	• Reusable	yes
• Design series	tesa® BABOO	• Reusable with	Powerstrips
• Dishwasher safe	no		Waterproof XL
• Hazard material	yes	• Solvent free	yes
• Material	Plastic, Bamboo	• Suitable surfaces	Glazed Tiles, Even wood, Most plastics, Glass, Metal, Marble
		• UV-resistant	no

Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

For latest information on this product please visit <http://l.tesa.com/?cp=NaN>