



tesa® Adhesive Strips for Transparent & Glass 0.2kg



Product Information

BNR 77732

Product Description

Refill pack for the Adhesive Hook for Transparent & Glass 0.2kg. For convenient reuse of the Adhesive Hook or to use alone. II Refill pack for the Adhesive Hook for Transparent & Glass 0.2kg. For convenient reuse of the Adhesive Hook or to use alone.

Product Features

- Strip for reuse of the Adhesive Hook 0.2kg
- For transparent and solid surfaces indoors
- For light weight objects up to 0.2kg per strip
- Strip can also be used alone without hook
- Removable without a trace I* Strip for reuse of the Adhesive Hook 0.2kg
- For transparent and solid surfaces indoors
- For light weight objects up to 0.2kg per strip
- Strip can also be used alone without hook
- Removable without a trace

Application Fields

How to apply – Step by step I 1. Before application, make sure the surface is free from grease and dirt with a silicone-free cleaner or methylated spirit.

2. After removing the foil, apply the Adhesive Strip to your surface. Press down for 5 seconds to activate the bonds. Be careful not to touch the adhesive area at any time.

3. If reusing an Adhesive Hook, apply it now. If using alone, press your object firmly on to the Adhesive Strip applying pressure for another 5 seconds.

4. If used alone, leave the tab free behind your object, so you can grab and pull it for easy removal.

II How to apply – Step by step 1. Before application, make sure the surface is free from grease and dirt with a silicone-free cleaner or methylated spirit.

2. After removing the foil, apply the Adhesive Strip to your surface. Press down for 5 seconds to activate the bonds. Be careful not to touch the adhesive area at any time.

3. If reusing an Adhesive Hook, apply it now. If using alone, press your object firmly on to the Adhesive Strip applying pressure for another 5 seconds.

4. If used alone, leave the tab free behind your object, so you can grab and pull it for easy removal.



tesa[®] Adhesive Strips for Transparent & Glass 0.2kg

Product Information

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

- | | | | |
|--------------------|------------------|--------------------------------|--------|
| • Type of adhesive | synthetic rubber | • Holding power of strip up to | 0.2 Kg |
| • Total thickness | 650 µm | | |

Properties/Performance Values

- | | | | |
|--------------------------------|--------|------------------------|-----|
| • Application temperature from | -15 °C | • Ozone resistance | yes |
| • Chemical resistance | no | • Residue free removal | yes |
| • Hazard material | no | • Solvent free | yes |
| • Humidity resistance | no | • UV-resistant | yes |
| • Material | _NULL | • Waterproof | no |
| • Oil and grease resistance | no | | |

Disclaimer

tesa[®] products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa[®] product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

For latest information on this product please visit <http://l.tesa.com/?cp=NaN>