

## tesa® 70499

## **Product Information**



## 1000µm double sided white bond & detach tape

## **Product Description**

tesa® 70499 is a double-sided mounting tape which can be easily removed by stretching the adhesive.

tesa® 70499 features:

- \* Thickness: 1000µm
- \* Very high bonding strength
- \* High push out and shock resistance
- \* Easy removability by stretching the adhesive
- \* Residue free removal even after long bonding time
- \* High performance also on LSE substrates

## Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

#### **Product Construction**

•	Backing	none	•	Color	white
•	Type of adhesive	specialty	•	Color of liner	brown
•	Type of liner	glassine	•	Thickness of liner	72 μm
	Total thickness	1000 um			

#### Properties/Performance Values

•	Removability after 14 days (23°C)	very good	•	Static shear resistance at 40°C	very good
•	Residue-free removability	yes	•	Temperature resistance long	60 °C
•	Solvent free	yes		term	
•	Static shear resistance at 23°C	very good	•	Temperature resistance short	90 °C
				term	



# tesa® 70499

## **Product Information**

#### Adhesion to Values

•	Aluminium (initial)	25 N/cm	•	PE (initial)	19 N/cm
•	Aluminium (after 14 days)	25 N/cm	•	PE (after 14 days)	19 N/cm
•	Magnesium (initial)	23 N/cm	•	Steel (initial)	29 N/cm
•	Magnesium (after 14 days)	23 N/cm	•	Steel (after 14 days)	29 N/cm

#### Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

