



# tesa<sup>®</sup> 4156 PV1



## Product Information

Specialty tape for film mounting

### Product Description

tesa<sup>®</sup> 4156 PV 1 is a specialty tape designed for film and negative masking. The tape is available as litho-red (colour 57).

- tesa<sup>®</sup> 4156 PV 1 is light and age resistant and is easily removed without splitting or tearing. It also does not leave adhesive residues.
- tesa<sup>®</sup> 4156 PV 1 is easily applied as the tape lies flat during positioning and is not prone to edge curling.
- tesa<sup>®</sup> 4156 PV 1 ensures secure masking with perfect edge definition.
- tesa<sup>®</sup> 4156 PV 1 is highly transparent to the human eye even without the use of a light table. Parts already masked therefore remain visible thus enabling accurate positioning of the tape.
- Due to its special properties tesa<sup>®</sup> 4156 PV 1 is also suitable for splicing of film.

\*tesa<sup>®</sup> 4156 PV 1 is recommended for use with tesa<sup>®</sup> litho dispensers 6082 and 6090. Specially designed for litho work the straight-edge blade does not leave a serrated edge.

### Application Fields

tesa<sup>®</sup> 4156 PV 1 is a specialty tape designed for film and negative mounting.

### Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

### Product Construction

- Backing material cellophane
- Total thickness 60 µm

### Disclaimer

tesa<sup>®</sup> products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa<sup>®</sup> product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

For latest information on this product please visit <http://l.tesa.com/?ip=04156>