

# tesa® Adhesive Hook for Transparent & Glass 0.2kg



# **Product Information**

**BNR 77734** 

# **Product Description**

Transparent Adhesive Hook holds up to 0.2kg per hook. Invisible mounting for decorations and medium weight objects on transparent and solid surfaces like glass.

#### **Product Features**

- · For transparent and solid surfaces indoors
- For light weight objects up to 0.2kg per hook
- · Removable without a trace
- · Reusable with a new strip
- · Limited UV-resistant

# **Application Fields**

How to apply – Step by step1. Clean the surface with silicone-free window cleaner or methylated spirit. Make sure the surface is dry before application.

- 2. Apply the Adhesive Strip first to the rougher surface. Be careful not to touch the adhesive area at any time.
- 3. Apply the hook, also pressing on it evenly all over for at least 5 seconds.
- 4. Make sure the tab is accessible for easy removal.

### Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

#### **Product Construction**

•	Type of adhesive	synthetic rubber	•	Hook shape	Triangular
•	Holding power up to	0.2 Kg	•	Silicone free	yes

# **Properties/Performance Values**

•	Application temperature from	-15 °C	•	Ozone resistance	yes
•	Chemical Resistance	no	•	Residue-free removability	yes
•	Hazard material	no	•	Reusable	yes
•	Humidity resistance	no	•	Solvent free	yes
•	Material	PS (polystyrene)	•	UV resistant	yes
•	Oil and grease resistance	no	•	Waterproof	no



# tesa® Adhesive Hook for Transparent & Glass 0.2kg

**Product Information** 

# Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.