



tesa[®] 54999 PV1

Product Information

PSA Tabbing Tape for an easy finger-lift solution

Product Description

tesa[®] 54999 PV1 is a green translucent tabbing tape featuring a PET backing with a silicone adhesive and a white finger lift.

Product Features

- Translucent for an easy and secure application
- High stiffness for good workability
- White finger-lift for accurate positioning
- tesa[®] 54999 is available on a special white PET liner

Application Fields

- Finger-lift for fast liner removal on roll application and die cuts
- For straight tabbing applications, commonly used for bridging to remove the liner from several pieces of tape and/or die cuts in just one operation

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

- | | | | |
|--------------------|----------------|-------------------|--------|
| • Backing | PET film | • Total thickness | 150 µm |
| • Type of adhesive | silicone based | • Color | green |
| • Type of liner | PET film | | |

Additional Information

Designed for manual tabbing tape application of royal blue liner of tesa[®] ACX^{plus} 78XX PV29 and 778XX PV15.

Standard dimensions:

- 10x30mm incl. 10mm finger-lift
- 6x30mm incl. 10mm finger-lift

Please refer to “Tips & Tricks for tesa[®] Tabbing Tapes” for application guidance.



tesa[®] 54999 PV1

Product Information

Disclaimer

tesa[®] products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa[®] product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit <http://l.tesa.com/?ip=54999>