




Product Information



$200\mu m$ d/s black high shock PE foam tape

Product Description

tesa[®] 66214 is a black double-sided tape consisting of a shock absorbing PE-foam backing equipped with a novel shock resistance adhesive.

Product Features

- Outstanding shock performance
- Outstanding anti-repulsion properties to prevent lifting issue
- Superior push-out resistance
- Good rework ability
- Waterproofness

Application Fields

- Screen, back cover & touch panel mounting for smart phone, watch, tablet, touch laptop, etc
- Camera lens mounting and deco mounting
- Display bottom for phone device

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

BackingType of adhesiveType of liner	PE foam modified acrylic PET film	Total thicknessColorThickness of liner	200 μm black 50 μm
Properties/Performance Values			
Elongation at breakTensile strength	190 % 9.3 N/cm	 Static shear resistance at 23°C Static shear resistance at 40°C 	very good good, medium
Adhesion to Values			
 ABS (initial) ABS (after 14 days) Glass (initial) Glass (after 14 days) PC (initial) PC (after 14 days) 	8.1 N/cm 9.9 N/cm 12.3 N/cm 13 N/cm 12.1 N/cm 14.9 N/cm	 PE (initial) PE (after 14 days) PMMA (initial) PMMA (after 14 days) Steel (initial) Steel (after 14 days) 	5 N/cm 5.8 N/cm 12.7 N/cm 16 N/cm 11 N/cm 14 N/cm





Product Information

Disclaimer

tesa[®] products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa[®] product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



Page 2 of 2 – as of 17/02/24 – en-US