




8694

Product Information



100µm translucent light curable structural bonding tape

Product Description

tesa® L-tape 8694 is a translucent light curable structural bonding tape. The curing process starts upon exposure to UV or blue light (standard 365 nm or 460 nm lamps). tesa® L-tape has initial tack for easy application of the adhesive before curing. Sufficient open time after activation allows bonding of both transparent and opaque components. tesa® L-tape comes with an immediate high bonding strength, which avoids additional fixation steps after initial bonding.

Product Features

- High bonding performance, even on small bonding areas and thin design gaps
- Tacky at room temperature
- Bonding of translucent or opaque substrates
- Immediate bonding strength after activation
- Easy die-cutting process (PET Reinforced)

Application Fields

tesa® L-tape is especially recommended for:

- Bonding of temperature sensitive substrates
- Component mounting in electronic devices

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

- | | | | |
|--------------------|------------|-------------------|-------------|
| • Backing | PET | • Total thickness | 100 µm |
| • Type of adhesive | UV-curable | • Color | translucent |
| • Type of liner | PET | | |

Product Assortment

- | | | | |
|--------------------|-------------|-------------------------|--------------|
| • Available colors | translucent | • Available thicknesses | 50, 100, 200 |
|--------------------|-------------|-------------------------|--------------|



8694

Product Information

Properties/Performance Values

• Tensile strength	_NULL N/cm	• Shelf life time (packed) < 15°C	_NULL months
• Activation temperature	25 °C	• Shelf life time (packed) < 25°C	_NULL months
• Bonding strength	10 N/mm ²	• Shelf life time (packed) < 5°C	_NULL months
• Bonding strength (dynamic shear)	10 N/mm ²	• Shelf life time < 15°C	_NULL months
• Bonding strength (push-out)	6.3 N/mm ²	• Shelf life time < 25°C	_NULL months
• Contact resistance z-direction	_NULL mOhm	• Shelf life time < 5°C	_NULL months
• DuPont	_NULL J	• Surface resistance x-y-direction	_NULL mOhm
• Push-out	_NULL N/cm		

Additional Information

tesa® L-tape is a reactive adhesive tape, which can be activated by wavelengths of 365 nm or 460 nm. tesa® L-tape can be used for bonding of transparent or opaque substrates. tesa® L-tape can be activated before or after lamination onto the first substrate. Transparent substrates such as clear plastics can be bonded before activation by light. At least one substrate must be light-permeable to enable the activation of tesa® L-tape. The bonded parts are then exposed to light to start curing of the adhesive.

Bonding of opaque substrates:

a) activation after lamination on the first substrate

At first, remove the covering liner of tesa® L-tape and laminate the tape onto the first substrate. The laminated parts are then exposed to light. The second substrate is bonded by applying sufficient pressure (≥ 3 bar) within 5 min after activation.

b) activation before lamination on the first substrate

At first, the die-cut of tesa® L-tape is activated by light. The covering liner of the die-cut must be light-permeable (e.g., clear PET) to enable the activation of the tape. After activation the die-cut is laminated onto the first substrate. The second substrate is then bonded by applying sufficient pressure (≥ 3 bar). Lamination and bonding must take place within 5 min after activation.

Lamination conditions

- Before curing tesa® L-tape has initial tack and can be laminated like a common PSA tape
- For any lamination step a pressure of at least 1 bar is recommended to ensure proper wet-out of the adhesive

Bonding and curing conditions

- Light source: Lamp of 365nm or 460nm
- Light dose: 20 - 50 J/cm² at 365nm or 30 - 60 J/cm² at 460nm

For latest information on this product please visit <http://l.tesa.com/?ip=08694>



8694

Product Information

Additional Information

- Activation time: ≥ 30 s
- Pressure: ≥ 3 bar
- Bonding time: ≥ 30 s

Bonding strength values were obtained under standard laboratory conditions. (Material: PC test specimen / bonding conditions: Light dose: 52 J/cm^2 at 460 nm; activation time: 45 s; pressure: 5 bar for 30 s).

To reach maximum bonding strength surfaces should be clean and dry.

Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit <http://l.tesa.com/?ip=08694>