



tesa® Professional 4470

Double-sided Precision Mask

Product Information

Double-sided Precision Mask to customize your masking area

Product Description

With tesa® 4470 Double-sided Precision Masking Tape you can protect not only edges, but much larger areas too, no matter what shape they are. Simply tailor-make the protection by using the material of your choice and stick it to the second side of the tape, ensuring clean edges and reducing re-works considerably. The tape is easily removed and is well-suited to outdoor jobs, too, as it's UV-resistant and very durable. The precision painter's tape tesa® 4470 consists of a particularly tearproof, flat Washi special base. It allows creating particularly precise, sharp and clean paint edges.

Product Features

- Indoor and outdoor application
- Large area masking for your individual needs
- Ideal for sharp paint edges

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

- Total thickness 160 µm

Properties/Performance Values

- | | | | |
|-----------------------|---------|--------------------|-----------|
| • Elongation at break | 5 % | • Sharp color edge | very good |
| • Tensile strength | 35 N/cm | • UV-resistance | 26 |
| • Hand tearability | good | | |

Adhesion to Values

- Steel 1.8 N/cm



tesa® Professional 4470 Double-sided Precision Mask

Product Information

Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit <http://l.tesa.com/?mp=04470>